

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, ILLINOIS


FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-RSX

REPLACES	BZ-RSX	
	M	
	DRAWING NUMBER	
	1215	
CHECK	ISSUE	1415
	REVISIONS	
	A CO 16325 GCH 14 JUNE 62	
	B CO-34307 JAL 22 JAN 76	
CHECK	C CO44156 SJS 20 APR 78	
	D CO77590	
	DLT 9 JUN 94	
	DAW 15 JUNE '82	
CHECK	DAW 15 JUNE '82	
	DAW 15 JUNE '82	
	DAW 15 JUNE '82	
	DAW 15 JUNE '82	
DRAWN	GCH 14 JUNE 62	
	GCH 14 JUNE 62	
	GCH 14 JUNE 62	
	GCH 14 JUNE 62	



NOTE -
 ▲ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE----- 7 - 9 1/2 OZ		CONTACT ARRANGEMENT		DO NOT SCALE PRINT	
OVERTRAVEL----- .025 MIN		SINGLE POLE DOUBLE THROW MAINTAINED CONTACT			
RESET CHARACTERISTICS		UL LISTED-FILE E12252		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:	
OPERATING FORCE----- 2-10 OZ		15A-125, 250 OR 480 VAC			
OVERTRAVEL----- .015 MIN		1/4 HP-125 VAC; 1/2 HP-250 VAC			
		1/2A-125 VDC; 1/4A-250 VDC			
		CODE L67			
				ONE PLACE (.0) ± .030	
				TWO PLACE (.00) ± .015	
				THREE PLACE (.000) ± .005	
				ANGLES ±	
				WEIGHT	