

MICRO SWITCH

FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL

FED MFG CODE 91928

SWITCH - ENCLOSED

CATALOG LISTING
BZE6-RQX2

BZE6-RQX2

M

DRAWING
NUMBER

9

ISSUE

3

PSR

CHECK

REVISIONS

A

24

B

2

C

8

D

E

14

F

G

BS

29AUG07

KPK

CHECK

24

AUG 77

RASTER

FO-92851-A

DRAWN

REPLACES

RELEASE NO

29AUG07

PSR

CHECK

1 SEP 77



ROB

CHECK

1 SEP 77

CHECK

24 AUG 77



NOTES-

- 1 - 6-32 UNC X .218 REF BINDING HEAD TERMINAL SCREW (3)
- 2 - FURNISHED UNASSEMBLED
- 3 - SEAL RATING: NEMA 1
IP40

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — 6-9 1/2 OZ	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
OVERTRAVEL — .187 MIN	SPDT MAINTAINED CONTACT	UNLESS OTHERWISE NOTED
RESET CHARACTERISTICS	15A-125, 250 OR 480 VAC	DIMENSIONS ARE IN INCHES
OPERATING FORCE — 8 OZ MIN	1/4 HP-125 VAC; 1/2 HP-250 VAC	TOLERANCES ARE:
BASIC SWITCH REPLACEMENT — BZ-RQX66	1/2A-125 VDC; 1/4A-250 VDC	ONE PLACE (0) ±.030
	CODE L67	TWO PLACE (.00) ±.015
	CE 1.5A, 240 Vac	THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT .60 LB