

NOTES:
 ① MAT'L: COPPER (STOCK TKN $\frac{040}{1.02}$)

PLATING: ELECTRO-TIN


STUD SIZES: (± 0.005)

02 = .094 209 = .209
 04 = .119 413 = .413
 06 = .146
 08 = .173
 10 = .198
 14 = .265
 56 = .328
 38 = .390

UL LISTING # E32244
 CSA LISTING # 18689

ALL DIMENSIONS = INCHES
 M M

WIRE SIZE: 12-10 AWG
 4.0-6.0 MM²



FILE NO. C-CD-101-01

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES	REFERENCE		TITLE:	
					SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
C-101-	$\frac{.750}{19.05}$	$\frac{.611}{15.52}$	$\frac{1.280}{32.51}$	14, 56, 38, 76, 12	SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
C-128-	$\frac{.375}{9.53}$	$\frac{.303}{7.70}$	$\frac{.785}{19.94}$	04, 06, 08, 10, 209	SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
C-130-	$\frac{.530}{13.46}$	$\frac{.393}{9.98}$	$\frac{.952}{24.18}$	10, 14, 56, 38	SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
C-136-	$\frac{.282}{7.16}$	$\frac{.306}{7.77}$	$\frac{.741}{18.82}$	04, 06, 08	SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
C-140-	$\frac{.592}{15.04}$	$\frac{.468}{11.89}$	$\frac{1.056}{26.82}$	10, 14, 56, 38, 209, 413	SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED					SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
FRAC. DEC. ANG.					SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
± ± ±					SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES
± ± ±					SCALE:	NTS	DATE	RING TONGUE TERMINAL KRIMP TITE 100-SERIES



DWG. NO. A CUSTOMER DWG.