


NOTES:

- ① MAT'L: COPPER, STOCK THK .031 \pm .001
PLATING: ELECTRO-TIN (.0003 MIN)
- ② TIN-PLATED BRASS FUNNEL FERRULE
- ③ NYLON INSULATION (BLUE)
- ④ UL LISTING #E32244
CSA LISTING 18689

FILE NO. BB-CD-805-03



MWID = MAX. WIRE INSULATION DIA.

WIRE SIZE: 16-14. AWG.
1.0-2.5 MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	"D" ±.005	AVAILABLE STUD SIZES	DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		SCALE: NTS	DATE	TITLE:	DWG. NO.
						DEC.	ANG.				
BB-8716	.310	.261	.886	.139	08 (.173 \pm .005)				4-5-85	SNAP SPADE SHORT TONGUE TERMINAL. AVIKRIMP-300 SERIES	A
BB-8717	.330	.261	.934	.156	10 (.198 \pm .005)						A



CUSTOMER DWG.