




Y	10	52.24	34.29	48.29	41.29		18.4	4		9	2-	-8
X	10	52.24	34.29	48.29	41.29		18.4	4		9	1-	-8
	8	44.62	26.67	40.67	33.67		18.4	4		7	1-	-7
	5	33.19	15.24	29.24	22.24		18.4	4		4	1-	-5
Y	3	25.57	7.62	21.62	14.62		8.4	2		2	2-	-3
X	3	25.57	7.62	21.62	14.62		8.4	2		2	1-177648-3	
キータイプ KEY TYPE	POS. 極数 寸法 DIMENSION	A	B	C	D		F	G		N	型番 PART NUMBER	

PRINT LIST

単位: mm DIN

CIRCUIT NO.
回路番号

Copyright © 1992 年				Copyright © 1992 AMP (Japan) LTD. ALL RIGHTS RESERVED.				AMP 日本エー・エム・ピー株式会社 Tokyo, Japan							
組合電線断面積 (WIRE RANGE)				被覆外径 (INSULATION DIA.)				名称 (NAME) フリーハンギングタイプタブ・ハウジング ダイナミック D3100S シリーズ用 WIRE TO WIRE TAB HSG FOR DYNAMIC 3100 (SINGLE ROW)							
B	REVISED (FJ00-3700-95)	KI	Y.I	24/NOV 95	- mm ² (AWG) -				一般公差 (GENERAL TOLERANCE)						
A1	REVISED (FJ00-2011-95)	NM	S.M	3/30 95	材料 (MATERIAL) 注記参照				SIZE LOC 番号 (No.)						
A	REVISED (FJ00-0685-94)	KI	S.M	9/27 94	仕上 (FINISH) SEE NOTES				B J 177648						
O	RELEASED J-1533	NM	S.M	11/16 92	DR. 9 NOV 92 N. Matsubara				100μT: ±0.2						
LTR	変更 (REVISION RECORD)			DR	CHK	DATE	CHK.	APP.	100μT: ±0.25						
							S. MANABE	S. MANABE	300μT: ±0.3						
									9 度: ±3°						
									尺度 (SCALE) 2/1						
									REV. B						
									SHEET 1 OF 1						