


8/51



	PIN OUT		
	(RJ45) J1	J2 (RJ45)	
PAIR-1	[1	1 WHITE/ORANGE	XX
	2	2 ORANGE	
PAIR-2	[3	3 WHITE/GREEN	XX
	6	6 GREEN	
PAIR-3	[4	4 BLUE	XX
	5	5 WHITE/BLUE	
PAIR-4	[7	7 WHITE/BROWN	XX
	8	8 BROWN	
	SHELL	SHELL	

- NOTES:
1. WIRE: CAT.5 STP 24AWG 4PRS STRANDED PATCH CABLE OD=6.0MM
JACKET COLOR: RED
 2. CONN: J1,J2-RJ45(8P8C)SHIELD PLUG W/2PRONG+50U" CRIMP TYPE+BOOT
 3. PIN OUT: T568B
 4. PLASTIC BOOT PVC MOLDING COLOR: RED
 5. ELECTRICAL TEST:
 - 1). 100% OPEN: SHORT TEST
 - 2). INSULATOR RESISTANCE: 1MΩ MIN

VER	ECN	DATE
1.1	MODIFY CABEL LENGTH	2000.10.18
1.2	ADD ITEM NO	2001.01.18
ITEM NO		LENGTH
1962-0.5R		0.5M+0.05M -0.03M
1962-1R		1M±0.05M
1962-2R		2M±0.05M
1962-3R		3M±0.05M
1962-5R		5M±0.05M

MOLD		INSIDE		OUTSIDE	
PLASTIC BOOT				2001022	
GW NO.		DWG NO	VD3-20		
CUS NO	AVD01	VER.	1.2		
DRAWN		SHEET.	1/1		
	<i>Shao Fuling</i>	SCALE.	1:1		
CHECKED		UNIT.	MM		
	杜红敏	DATE.	OCT 19. 2000		
APPROVED					
				TITLE: CAT.5 STP STRAND 4PRS PATCH CABLE	