




9A03			
P1		P2	
1	—	1	SHIELD
2	—	2	WHITE
3	—	3	WHITE
4	—	4	SHIELD
4	—	4	SHIELD
5	—	5	WHITE
6	—	6	WHITE
7	—	7	SHIELD
SHIELD	—	SHIELD	—

⚠ * NOTE: All relevant materials are complied with RoHS directive .

3	MOLDED PVC BLACK		M304
2	UL2725 SERIAL ATA EXTERNAL CABLE, (26AWG*2C+AM)*2PCS+3D+PVC+B, OD 3.9*9.3mm, JACKET RED (R525F)	1000mm	M298
1	SATA CONNECTOR, FEMALE 7 PIN WITH METAL CASE, BLACK INSULATOR(SECOND SATA)	2Set	M108
No.	DESCRIPTION		Q'TY Supplier
APPROVED		RB-441	
CHECKED	TIAN		
DRAWING	SONG		
DATE	23/NOV/05	ITEM NO.	9A03
		UNIT:mm	

Cable Length Unless Other Spec. Tolerances:	
0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm