

# ARIANTE 25-30



## FEATURES

- Rotating Grille Fan
- Speed control
- Pole motor with thermal overload protection
- Switches for selecting speed and activating rotating grille
- Front and back grilles removable for easy cleaning

## MODELS

Type	Code	Farnell code	Specification
Ariante 25	60797	7002786	370mm high x 370mm wide x 155mm deep. Finished in dive grey
Ariante 30	60796	-	440mm high x 440mm wide x 175mm deep. Finished in dive grey
Ariante 30 Arlecchino	60799	-	Features & dimensions same as Ariante 30. However, Arlecchino's various parts come in 5 pastel shades: yellow, grey, pink, light blue and light green. Each unit is unique in appearance as there are 78125 possible colour combinations.

# ARIANTE TOWER

## FEATURES

- Rotating Free-standing Floor Fan
- 3 speed control
- Thermal overload protected motor.
- 2 switches for selecting speed and activity of fan
- Inovative design for space saving whilst in use

## MODEL

Type	Code	Farnell code	Specification
Tower fan	63009	7002841	732mm x 17mm. Available in dove grey.