

INTERNAL TOOLHOLDERS

711-9422



S...PTFNR 91°

| PART NO. ISO | CODE NO. | PRICE £ EACH | SPARE PARTS | | | | | | |
|--------------------------------|-----------|-----------------|---------------------------------|---------------------------|-----------------------------|---------------------------|---------------------------|------------------|---------------------------|
| | | | INSERTS | ANVIL | PIN | WEDGE | LOCKING SCREW | KEY mm | PUNCH |
| S25T PTFNR-16 S32U PTFNR-16 | 6-229-251 | 73.00 | TNMA TNMG TNMM 1604... | 177.26-622 (6-403-050) | 117.26-650.2 (6-405-048) | 110.26-640 (6-405-002) | 117.26-655 (6-405-046) | 3 (6-412-003) | 117.26-686 (6-402-026) |
| | 6-229-321 | 76.00 | | | | | | | |
| S50V PTFNR-22 | 6-229-501 | 110.00 | TNMA TNMG TNMM 2204... | 170.26-624 (6-403-070) | 170.26-650.1 (6-405-057) | 110.26-642 (6-405-006) | 117.26-655 (6-405-058) | 4 (6-412-004) | 117.26-687 (6-402-027) |

NOTE: Carbide inserts see pages 98 and 107 Spare parts see pages 141 and 142



S...SCLCR 95°

| PART NO. ISO | CODE NO. | PRICE £ EACH | SPARE PARTS | | |
|---|-------------------------------------|-------------------------|-----------------------|-----------------------|---------------------|
| | | | INSERTS | LOCKING SCREW | KEY mm |
| S08H SCLCR-06 S08K SCLCR-06 S10K SCLCR-06 | 6-292-071 | 36.65 | CCGT, CCMT 0602... | S-2506 (6-404-080) | T-7 (6-412-020) |
| | 6-292-081 | 36.65 | | | |
| | 6-292-101 | 36.65 | | | |
| S12M SCLCR-09 S16R SCLCR-09 S20S SCLCR-09 | 6-292-121 6-292-161 6-292-201 | 38.10 40.00 48.00 | CCGT, CCMT 09T3... | S-4008 (6-404-082) | T-15 (6-412-022) |


NOTE: Carbide inserts see pages 97 and 106 Spare parts see pages 141 and 142



E...SCLCR/L 95° - SOLID CARBIDE SHANK

| PART NO. ISO | CODE NO. | PRICE £ EACH | SPARE PARTS | | | | | |
|--|---|--|--------------------|-------------------------|----------------------|--------------------|-------------------------|----------------------|
| | | | INSERTS | LOCKING SCREW | KEY mm | | | |
| E08K-SCLCR06 E08K-SCLCL06 E10M-SCLCR06 E10M-SCLCL06 E12M-SCLCR06 E12M-SCLCL06 | 6-295-008 6-295-009 6-295-010 6-295-011 6-295-012 6-295-0132 | 203.00 203.00 216.00 216.00 220.00 220.00 | CCGT, CCMT 0602... | FTGA2565 (6-408-412) | TW07P (6-407-607) | | | |
| E16R-SCLCR09 E16R-SCLCL09 E20S-SCLCR09 E20S-SCLCL09 | 6-295-016 6-295-017 6-295-020 6-295-021 | 226.00 226.00 300.00 300.00 | | | | CCGT, CCMT 09T3... | FTGA3508 (6-408-416) | TW15P (6-407-615) |

NOTE: Carbide inserts see pages 97 and 106 Spare parts see page 143



S...SDQCR 107° 30'

| PART NO. ISO | CODE NO. | PRICE £ EACH | SPARE PARTS | | |
|--------------------------------|------------------------|-----------------|-----------------------|-----------------------|---------------------|
| | | | INSERTS | LOCKING SCREW | KEY mm |
| S20S SDQCR-11 S25T SDQCR-11 | 6-182-201 6-182-251 | 48.00 62.00 | DCGT, DCMT 11T3... | S-4008 (6-404-082) | T-15 (6-412-022) |

NOTE: Carbide inserts see pages 97 and 106 Spare parts see pages 141 and 142



S...SDUCR 93°

| PART NO. ISO | CODE NO. | PRICE £ EACH | SPARE PARTS | | |
|--------------------------------|------------------------|-----------------|-----------------------|-----------------------|---------------------|
| | | | INSERTS | LOCKING SCREW | KEY mm |
| S20S SDUCR-11 S25T SDUCR-11 | 6-181-201 6-181-251 | 48.00 62.00 | DCGT, DCMT 11T3... | S-4008 (6-404-082) | T-15 (6-412-022) |

NOTE: Carbide inserts see pages 97 and 106 Spare parts see pages 141 and 142