

# Product Data Sheet - G032

887 663

## General

Description: TB720 TURBO CABLE 20'

Date: 06/09/96

Manufacturer: KL017

Part No.:

Status: Current

Product Type: Catalogue

Country Variant

Replaces:

Replaced By:

### Product Notes:

Guitar leads  
Professional quality double screened  
Sheathed in black  
Mono jack plug to mono jack plug, both have metallic bodies  
Moulded-on strain relief  
Noiseless guitar lead

### Technical Specification:

Guitar lead with jack plug connectors  
Cable diameter: 5.64mm  
Screening: oxygen free copper  
Sheathing: neoprene  
6.35mm jack plugs: diameter: 12.06mm length: 120.44mm  
Frequency range: 20Hz to 20kHz  
Characteristic impedance: 76.295ohm/km  
Strand /conductor: 20 x 0.12  
Cross sectional area: 0.226mmsq  
Lead insulation material: PVC 810  
Temperature range: 300V at 60°C  
Voltage rating: 150V  
Fax ref: JP53

## Physical

Accs included:

Dimensions W: 0 mm H: 0 mm D: 6000 mm Dia: 12.06 mm

Weight: 0.379 kg

## Power

Supply Voltage:

Internal Fuse:

Supply Type:

Consumption:

Plug Type:

Battery Type:

Plug Fuse:

No. of Batteries: N/A