



### SPECIFICATIONS

Min. No Load Voltage	6.2V
Min. On Load Voltage	3.8V on 3 amps at 500ms
Rated Capacity	1400mAh on 200Ω to 4V
Min. Life	40Hrs on 200 Ω to 4V
Volume	20 cm <sup>3</sup>
Weight	38 g

