



BNT-2000AP



GENERAL INFORMATION

Model Type BLACK KNIGHT PRO
 Model Name BNT-2000AP

AC INPUT

AC Input Capacity on Battery 2000VA
 AC Input Voltage 100V or 110V/120V or 220V/230V/240V +/- 25% at line input
 AC Input Frequency 50/60 Hz +/-0.5% (auto sensing)
 AC Input Transfer N/A

AC OUTPUT

AC Output Voltage Simulated sine wave at 100V or 110V/ 115V/ 120V or 220V/ 230V/ 240V
 AC Output Frequency 50/60 Hz +/-0.5%
 AC Output Voltage Regulation AVR automatically increase output voltage 15% above input voltage
 AC Output Transfer 2/4 milliseconds, including detection time

PROTECTION

Protection Spike 480 Joules / 2ms
 Protection Overload UPS automatic shutdown if overload exceeds 110% nominal at 60 sec and 130% at 3 sec
 Protection Unit Fuse for overload & short circuit protection
 Protection Inside Protection UPS output cut off immediately or input fuse protection

BATTERY

Battery Type sealed, maintenance-free lead acid batteries
 Battery Typical 6 hours (to 90% of full capacity)
 Battery Protection Auto discharge protection

Battery Run Time	70 - 80 minutes
------------------	-----------------

PHYSICAL

Physical Weight kgs	14.5
Physical Weight lbs	31.9
Physical Shipping Weight kgs	15.9
Physical Shipping Weight lbs	35
Physical Dimension mm	382x130x192
Physical Dimension inch	15.0

INDICATOR

LED	LED
-----	-----

ALARM

Alarm Battery Backup	Slow beeping sound (about 0.47 Hz)
Alarm Battery Low	Rapid beeping sound (about 1 Hz)
Alarm Overload	Continue beeping sound

INTERFACE

Interface RS-232	YES
------------------	-----

ENVIRONMENT

Environment Ambient	3,500 meters max. elevation, 0-95% humidity non-condensing
Environment Audible	<40dBA (1 meter from surface)
Environment Storage Condition	15,000 meters max. elevation
ShowOrder	0

Copyright 2002 Powercom America Inc. 623 South State College Blvd., Fullerton, California 92831 USA
Powered by GUS Networks, Inc.
All rights reserved.