


Catalogue:

Chapter:

Wrenches and spanners

Section:

Adjustable wrenches


Traditional models, Phosphated, 31/86/87

As per DIN 3117 Form A, angle 15° (reference 10, 31) and 22.5° (reference 86, 87) BS 6333, ISO 6787 and ASME B107.8M-1996.

Finish: Phosphated. Traditional models, where the 10 model is equipped with measuring scale and one end shaped to remove bicycle tyres etc. 31 model with measuring scale and alligator jaw. The alligator jaw is used as a pipewrench.

IP = Industrial pack.



| | EAN 731415+ | | A mm | B mm | C mm | D mm | g |
|-------|----------------|----|---------|---------|---------|---------|------|
| 31 | 0004942 | 5 | 205 | 32 | 5.5 | 13.5 | 270 |
| 86 | 0005376 | 1 | 614 | 63 | 27.5 | 29.0 | 3165 |
| 87 | 0005406 | 1 | 770 | 85 | 31.0 | 33.0 | 5700 |
| 31 IP | 0004959 | 50 | 205 | 32 | 5.5 | 13.5 | 270 |


80-series, Phosphated, 80

As per DIN 3117 Form A, angle 15°, BS 6333, ISO 6787 and ASME B107.8M-1996.

Finish: Phosphated. Precision-hardened and anti-corrosion treated.

Series P: combination of pipe grip facility, one side serrated, may be used as a pipe wrench. Left-reading, measurement scale in mm.

IP = Industrial pack



| | EAN 731415+ | | A mm | B mm | C mm | D mm | g |
|------|----------------|---|---------|---------|---------|---------|-----|
| 8069 | 0007028 | 5 | 110 | 13 | 4.0 | 9.0 | 60 |
| 8070 | 0007110 | 5 | 155 | 20 | 4.9 | 11.3 | 135 |
| 8071 | 0007202 | 5 | 205 | 27 | 6.0 | 12.9 | 255 |
| 8072 | 0007288 | 5 | 255 | 30 | 8.6 | 15.5 | 400 |