

MV8132

| Attribute | | Value | UOM |
|--------------------------------------|-------------|--------------|-----|
| Number of Colors | | Single | |
| Source | Color | Red (AlGaAs) | |
| | Brightness | Standard | |
| Forward Voltage (V _F) | TYP | 1.7 | V |
| | MAX | 2.4 | V |
| Peak Wavelength | | 660 | nm |
| Luminous Intensity (I _v) | MIN | 630 | mcd |
| | TYP | 940 | mcd |
| Package | | T-1 3/4 | |
| Lens | Diffusivity | Water Clear | |
| Viewing Angle | | 30 | deg |
| Forward Current | | 40 | mA |
| Spectral Line Half Width | | 20 | nm |
| Peak Current | | 200 | mA |
| Power Dissipation | | 110 | mW |