

Molex Europe Kits BOM			
Part number	Included parts	Description	Quantity
76650-3014	43025-0200	Micro-Fit 3.0™ receptacle, dual row	10
	43025-0400	Micro-Fit 3.0™ receptacle, dual row	10
	43025-0600	Micro-Fit 3.0™ receptacle, dual row	10
	43025-0800	Micro-Fit 3.0™ receptacle, dual row	10
	43025-1000	Micro-Fit 3.0™ receptacle, dual row	5
	43025-1200	Micro-Fit 3.0™ receptacle, dual row	5
	43045-0212	Micro-Fit 3.0™ vertical header, dual row, through hole, OTR, tin plated, 02ckts	10
	43045-0412	Micro-Fit 3.0™ vertical header, dual row, through hole, OTR, tin plated, 04ckts	10
	43045-0612	Micro-Fit 3.0™ vertical header, dual row, through hole, OTR, tin plated, 06ckts	10
	43045-0812	Micro-Fit 3.0™ vertical header, dual row, through hole, OTR, tin plated, 08ckts	10
	43045-1012	Micro-Fit 3.0™ vertical header, dual row, through hole, OTR, tin plated, 10ckts	5
	43045-1212	Micro-Fit 3.0™ vertical header, dual row, through hole, OTR, tin plated, 12ckts	5
	43045-0200	Micro-Fit 3.0™ right angle header, dual row, through hole, snap-in peg, tin plated, 02ckts	10
	43045-0400	Micro-Fit 3.0™ right angle header, dual row, through hole, snap-in peg, tin plated, 04ckts	10
	43045-0600	Micro-Fit 3.0™ right angle header, dual row, through hole, snap-in peg, tin plated, 06ckts	10
	43045-0800	Micro-Fit 3.0™ right angle header, dual row, through hole, snap-in peg, tin plated, 08ckts	10
	43045-1000	Micro-Fit 3.0™ right angle header, dual row, through hole, snap-in peg, tin plated, 10ckts	5
	43045-1200	Micro-Fit 3.0™ right angle header, dual row, through hole, snap-in peg, tin plated, 12ckts	5
	43030-0007	Micro-Fit 3.0™ female crimp terminal, 20-24AWG, tin plated, loose piece	100
	11-03-0043	Extraction tool	1