

Molex Europe Kits BOM			
Part number	Included parts	Description	Quantity
76650-3015	43025-0200	Micro-Fit 3.0™ receptacle, dual row	10
	43025-0400	Micro-Fit 3.0™ receptacle, dual row	10
	43025-0600	Micro-Fit 3.0™ receptacle, dual row	10
	43025-0800	Micro-Fit 3.0™ receptacle, dual row	10
	43025-1000	Micro-Fit 3.0™ receptacle, dual row	5
	43025-1200	Micro-Fit 3.0™ receptacle, dual row	5
	43045-0218	Micro-Fit 3.0™ vertical header, dual row, SMT, Fitting nail, tin plated, 02ckts	10
	43045-0418	Micro-Fit 3.0™ vertical header, dual row, SMT, Fitting nail, tin plated, 04ckts	10
	43045-0618	Micro-Fit 3.0™ vertical header, dual row, SMT, Fitting nail, tin plated, 06ckts	10
	43045-0818	Micro-Fit 3.0™ vertical header, dual row, SMT, Fitting nail, tin plated, 08ckts	10
	43045-1018	Micro-Fit 3.0™ vertical header, dual row, SMT, Fitting nail, tin plated, 10ckts	5
	43045-1218	Micro-Fit 3.0™ vertical header, dual row, SMT, Fitting nail, tin plated, 12ckts	5
	43045-0209	Micro-Fit 3.0™ right angle header, dual row, SMT, Fitting nail, tin plated, 02ckts	10
	43045-0409	Micro-Fit 3.0™ right angle header, dual row, SMT, Fitting nail, tin plated, 04ckts	10
	43045-0609	Micro-Fit 3.0™ right angle header, dual row, SMT, Fitting nail, tin plated, 06ckts	10
	43045-0809	Micro-Fit 3.0™ right angle header, dual row, SMT, Fitting nail, tin plated, 08ckts	10
	43045-1009	Micro-Fit 3.0™ right angle header, dual row, SMT, Fitting nail, tin plated, 10ckts	5
	43045-1209	Micro-Fit 3.0™ right angle header, dual row, SMT, Fitting nail, tin plated, 12ckts	5
	43030-0007	Micro-Fit 3.0™ female crimp terminal, 20-24AWG, tin plated, loose piece	100
	11-03-0043	Extraction tool	1