

CP68, 2280 & 2290 Series




CP-68

MODEL	DIM. A MM (INCHES)	R_{θ} (°C/W)
CP68	-----	21.7
2283B	-----	32.6
2286B	-----	32.6
2288B	25.40 (1.000)	25.9



MODEL	DIM. A MM (INCHES)	R_{θ} (°C/W)
2292B	28.58 (1.125)	23.4
2296B	-----	18.8
2297B	31.75 (1.250)	17.9
2298B	38.10 (1.500)	16.3




▲ CP68




▼ CP68





▲ 2296B




▼ 2283





▼ 2296



▼ 2286



▼ 2297, 2298



▼ 2288, 2292

