



SANDFLEX®

Bi-metal blades

3840





Virtually unbreakable Sandflex bi-metal blade for all materials and type of cut.

Standard for fast and aggressive straight cuts.

Slope for various types of cuts.

Scroll for contour sawing and in difficult-to-reach places.

Product code	EAN code 731151+	Blade length mm	Tooth shape	Standard 	Slope 	Scroll 	
5 blades per package							
3840-100-ST-6-5P	8883447	100	R-6	*			58
3840-100-ST-10-5P	8881641	100	R-10	*			58
3840-100-ST-14-5P	8881610	100	R-14	*			58
3840-100-ST-18-5P	8881627	100	R-18	*			58
3840-100-ST-24-5P	8881634	100	R-24	*			58
3840-100-SL-V6-5P	8879860	100	V6		*		48
3840-100-SC-10-5P	8881542	100	R-10			*	33
3840-100-SC-14-5P	8881511	100	R-14			*	33
3840-100-SC-18-5P	8881528	100	R-18			*	33
3840-150-ST-6-5P	8881665	150	R-6	*			97
3840-150-ST-10-5P	8881764	150	R-10	*			97
3840-150-ST-14-5P	8881771	150	R-14	*			97
3840-150-ST-18-5P	8881788	150	R-18	*			97
3840-150-ST-24-5P	8881795	150	R-24	*			97
3840-150-ST-8/12-5P	8882167	150	8/12	*			97
3840-150-SL-5/8-5P	8881429	150	5/8		*		90
3840-150-SC-4/6-5P	8881436	150	4/6			*	80
3840-200-ST-8/12-5P	8882174	200	8/12	*			180
3840-200-ST-14-5P	8881467	200	R-14	*			180
3840-200-SL-6-5P	8881443	200	R-6		*		160
3840-300-ST-8/12-5P	8882181	300	8/12	*			245
3840-300-ST-14-5P	8881474	300	R-14	*			225
3840-300-SL-6-5P	8881450	300	R-6		*		225
Bulk packed, 1000 blades per package							
3840-150-ST-14-1000P	8881900	150	R-14	*			18.600
3840-150-ST-18-1000P	8881887	150	R-18	*			18.600
3840-150-SL-5/8-1000P	8881894	150	5/8		*		18.600
Kits							
3840-SET-5	8879204	Contains 1 blade each of: 3842-150-SL-6, 3840-100-SC-10, 3840-150-ST-14, 3840-150-ST-18, 3840-150-ST-24					96
3840-SET-10	8888886	3840-100-ST-14, 3840-100-ST-18, 3840-150-ST-6, 3840-150-ST-14, 3840-150-ST-18					96
3840-SET-ST-5	8889999	3841-150-ST-6, 3841-150-ST-10, 3842-150-SL-6, 3840-100-ST-6, 3840-100-SC-10, 3840-100-SC-18 3840-100-ST-14, 3840-100-ST-24, 3840-150-ST-10, 3840-150-ST-14					196



PALLET AND CAR BODY SAWBLADES



SANDVIK

Especially developed sawblades for repairing of transport pallets. Blades produced in SANDFLEX® bi-metal, 24 TPI. Used in pneumatic machines type Cengar or similar. Tooth material Matrix II and blade thickness 0,75 mm. Available in 220 mm or 260 mm blade lengths.

The blades are packed in a hard plastic box of 100 pieces.

SANDFLEX® Pallet sawblades

3840

Product code	EAN code 731151+		Length mm	
3840-220-24	8182366	100	220	16
3840-260-24	8182373	100	260	19



Car body sawblades for pneumatic and electrical machines, type Shinano, Chicago-pneumatic or similar. Mostly used in car body workshops.

SANDFLEX® bi-metal, tooth material M2, for effective performance and long lasting blade life.

Packed in easy-to-use hard plastic cassette of 10 pieces or in bulk variants of 100 pieces.

SANDFLEX® Car body sawblades

3845

Product code	EAN code 731151+		Teeth /inch	Length mm	
10 blades per package					
3845-18-10P	8101602	1	18	90	48
3845-24-10P	8101619	1	24	90	48
3845-32-10P	8101626	1	32	90	48
Bulk (100 blades per box)					
3845-18-100P-BULK	8202361	1	18	90	48
3845-24-100P-BULK	8202378	1	24	90	48
3845-32-100P-BULK	8202385	1	32	90	48

