

289-760

Product Specification Sheet**GLO6** JCR215

Description: Rigger type glove c/w candy style striped fabric to cuff and back, bottom split leather, dye cut to palm, fingers and knuckles. A bound edge pasted safety cuff with candy striped fabric. Lined palm for extra user comfort. Internal elastics to back for secure fit.

Application: The gloves have been designed specifically for use in low hazard light industrial working environments that require a general purpose glove with excellent dry grip and abrasion resistance properties. The gloves are also suitable for use with medium duty general handling applications. Ideal for warehousing, construction and maintenance work.

Length: Overall length: 25cm (10")
Width across palm: 13cm
Middle fingertip to cuff: 25cm
Cuff Length: 7cm
Thumb and palm length: 17.5cm

Size: Size 10- Mens

Category: Category One. Minimal Risks Only. CE Marked



Packaging: 10 pairs /pack
12 packs/box
120prs Total/box