

Farnell 211-837 to 862

Information re UHF/VHF Amplifier specifications.

**Info re Am339 is the same as for the AM346 & AM347.
The AM340 has a slightly different gain on its outlets
as listed below.**

Safety Features

Insulation	Double
Internal fusing	Thermal to BS415
External fusing	Use 3amp fuse in mains plug
Mains Supply	AC220 –240v 50Hz
Safety	To BS415 – IEC 65
Fitting	Fit to solid flat surface using screws provided

Technical Features

Noise figure	2.5dB typical
Gain	12dB each out put for 1 3 & 4 set amps (<i>9db on AM340</i>)
Input/output	75 Ohms
Consumption	Less than 5 watts
Guarantee	5 years from data of purchase