



Features

- 2 RS232 Serial Ports
- COM1 COM8
- Interrupts 2-7,10-12, 14-15
- Massive 128 Byte FIFO on each port
- Utility disk with Sample programs, Test and Terminal software with source code
- Drivers for all popular operating systems

Specifications

Ports: 2 x RS232UART: 16950

Baud rates: Up to 230,400

Data Bits: 5,6,7 or 8Stop Bits: 1 or 2

• Parity: Odd, even, none,

mark or space

Power: 300mA @ 5V.

50mA @ ±12V

• Weight: 0.083kg

• Size: 10 x 12.5cm

Applications

- Modem Connectivity
- Remote Access Servers
- Instrument Control
- UPS Control
- Banking & Financial Sector

ISA

2 Port Photon RS232

Description





This half size card provides 2 industry standard 9 pin RS232 serial COM ports. Each serial port may be jumper configured as COM1 - COM8 with interrupt line jumpers set to IRQ 2-7, 10-12, 14-15.

The fast UART and line drivers give a maximum data rate of 230,400 baud.

Software

Serial Solutions Device Driver CD contains software for Windows Millennium, Windows 98, Windows 95, Windows NT4, Windows 3.x, DOS and OS/2.

Informative manuals and sample programs are supplied with full source code on CD!

For details of RS232, RS422 or RS485 Standards see: www.brainboxes.com/standards



ORDER

Description
ISA 2PORT PHOTON RS232

Code CC-479