



Features

- 2 RS232 Serial Ports, LPT port optional extra
- PCI Bus - Fully Plug & Play auto configuring interrupt and address
- Sample Programs, Test & Terminal software - all with source code
- Drivers for all popular operating systems

Specifications

- Ports: 2 x RS232
- UART: 16550
- Baud rates: Up to 115,200
- Data Bits: 5,6,7 or 8
- Stop Bits: 1 or 2
- Parity: Odd, even, none, mark or space
- Power: 190mA @ 5V
12mA @ 12V
- Weight: 0.097Kg
- Size: 8.5cm x 12.5cm

Applications

- Modem Connectivity
- Remote Access Servers
- Instrument Control
- UPS Control
- Laptop Docking Stations
- Banking & Financial Sector

PCI

2 Port RS232 (1x9, 1x25)

Description



This half size card provides 1 industry standard 9 pin and 1 industry standard 25 pin RS232 serial COM port in a single PCI slot. An LPT port can be added to the card using the optional LPT adaptor cable.

As PCI is fully Plug & Play compatible the operating system or Bios automatically configures the card ensuring conflict free installation.

Software

Serial Solutions Device Driver CD contains software for Windows XP, Windows 2000, Windows Millennium, Windows 98, Windows 95, Windows NT4, Windows 3.x, DOS and OS/2.

Informative manuals and sample programs are supplied with full source code on CD!

For details of RS232, RS422 or RS485 Standards see: www.brainboxes.com/standards



ORDER

Description	Code
PCI 2PORT RS232 (1x9, 1x25pin)	CC-250
Optional LPT Adaptor Cable	CC-032