



Model/ lamp reference	Fig. no.	Wattage	Base	Luminous flux	Colour rendering group	Length	Dia- meter	Weight	Light colour
OSRAM DULUX® EL LONGLIFE									
DEL LL 5	2	5 W	E27/B22d	240 lm	1B	121±2 mm	36 mm	60 g	41-827
DEL LL 7	2	7 W	E27/B22d	400 lm	1B	129±3 mm	45 mm	70 g	41-827, 21-840
DEL LL 11	2	11 W	E27/B22d	600 lm*	1B	138±3 mm	45 mm	75 g	41-827, 21-840, 11-860
DEL LL 15**	1	15 W	E27/B22d	900 lm*	1B	140±3 mm	52 mm	92 g	41-827, 21-840, 11-860
DEL LL 20**	1	20 W	E27/B22d	1200 lm*	1B	153.5±3 mm	52 mm	95 g	41-827, 21-840, 11-860
DEL LL 23	1	23 W	E27/B22d	1500 lm*	1B	173±3 mm	58 mm	100 g	41-827, 21-840, 11-860
DEL LL 3 E14	4	3 W	E14	100 lm	1B	115±2 mm	30 mm	35 g	41-827
DEL LL 5 E14	3	5 W	E14	240 lm	1B	124±2 mm	36 mm	55 g	41-827
DEL LL 7 E14	3	7 W	E14	400 lm	1B	134±3 mm	45 mm	65 g	41-827
DEL LL 11 E14	3	11 W	E14	600 lm	1B	143±3 mm	45 mm	65 g	41-827
OSRAM DULUX® EL CLASSIC									
DEL CL B 5 E14	7	5 W	E14	150 lm	1B	131±2 mm	46 mm	64 g	41-827
DEL CL A 5	6	5 W	E27/B22d	150 lm	1B	111±2 mm	60 mm	65 g	41-827
DEL CL A 7	6	7 W	E27/B22d	350 lm	1B	111±2 mm	60 mm	65 g	41-827
DEL CL A 11	5	11 W	E27/B22d	500 lm	1B	147±2 mm	70 mm	88 g	41-827
DEL CL A 15	5	15 W	E27/B22d	800 lm	1B	149.5±2 mm	70 mm	146 g	41-827
OSRAM DULUX® EL SENSOR									
DEL 15 SENSOR	1	15 W	E27/B22d	900 lm	1B	148±3 mm	52 mm	125 g	41-827
OSRAM DULUX® EL VARIO									
DEL VAR 23	1	23 W	E27/B22d	1500 lm	1B	173±3 mm	58 mm	110 g	41-827
OSRAM DULUX® EL GLOBE									
DEL GL 15**	8	15 W	E27/B22d	700 lm*	1B	169±2 mm	97 mm	150 g	41-827, 11-860
DEL GL 20	8	20 W	E27/B22d	1000 lm*	1B	190±2 mm	117 mm	155 g	41-827, 11-860
OSRAM DULUX® EL REFLECTOR									
DEL REFL 15	9	15 W	E27	335 cd	1B	143±2 mm	102 mm	145 g	41-827
DEL REFL 20	9	20 W	E27	450 cd	1B	161±2 mm	117.5 mm	170 g	41-827
OSRAM DULUX® EL ECONOMY									
DEL ECO 8 E14	3	8 W	E14	400 lm	1B	134±3 mm	45 mm	65 g	41-827
DEL ECO 12 E14	3	12 W	E14	600 lm	1B	143±3 mm	45 mm	70 g	41-827
DEL ECO 8	2	8 W	E27	400 lm	1B	129±3 mm	45 mm	65 g	41-827, 21-840
DEL ECO 12	2	12 W	E27/B22d	600 lm*	1B	138±3 mm	45 mm	70 g	41-827, 21-840, 11-860
DEL ECO 16	1	16 W	E27/B22d	900 lm*	1B	140±3 mm	52 mm	92 g	41-827, 21-840, 11-860
DEL ECO 21	1	21 W	E27/B22d	1200 lm*	1B	153.5±3 mm	52 mm	98 g	41-827, 21-840, 11-860
OSRAM DULUX® EL ECONOMY CLASSIC									
DEL ECO CL A 8	5	8 W	E27	340 lm	1B	147±2 mm	70 mm	88 g	41-827
DEL ECO CL A 12.5		12 W	E27/B22d	450 lm	1B	147±2 mm	70 mm	88 g	41-827
DEL ECO CL A 16.5		16 W	E27/B22d	600 lm	1B	149.5±2 mm	70 mm	146 g	41-827
OSRAM DULUX® EL ECONOMY GLOBE									
DEL ECO GL 16	8	16 W	E27	700 lm	1B	169±2 mm	97 mm	150 g	41-827
DEL ECO GL 21	8	21 W	E27	1000 lm	1B	190±2 mm	117 mm	155 g	41-827
OSRAM CIRCOLUX® EL									
CIRCO EL 18	10	18 W	E27	1000 lm	1B	101 mm	169 mm	210 g	41-827
CIRCO EL 24	10	24 W	E27	1700 lm	1B	99 mm	225 mm	170 g	41-827, 21-840

OSRAM GmbH
Hellabrunner Strasse 1
81543 Muenchen
Tel.: +49-89-6213-0
Fax: +49-89-6213-2020
<http://www.osram.de>
<http://www.osram.com>
<http://www.osram.de/lightatwork/>
<http://www.osram.com/lightatwork/>

Supply voltage 220–240 V. Not suitable for use on dimmer circuits or electronic switches.
Use outdoors only in air circulated enclosed luminaires.

* 5% less with colour 11-860 day light

Please note:

From summer 2001 the OSRAM light colour numbers will be dropped from the lamp references and only the international light colour numbers will be used.



THERE IS LIGHT. AND THERE IS OSRAM.

OSRAM

