

151-557


HIGH BREAKING CAPACITY
CERAMIC CARTRIDGE SILVERED CAPS

TIME - LAG

Beswick Type Ref
T TDC 459

DISTRIBUTIC A

SPECIFICATION



MARKING
BARREL PRINT.
ALERT.
T RATED CURRENT.
RATED VOLTAGE


RATED CURRENT	MAX mV DROP @ In		RATED VOLTAGE	
	In		AC	
1A	350		250	
1.25A	300		250	
1.6A	250		250	
2A	250		250	
2.5A	200		250	
3.15A	180		250	
4A	160		250	
5A	150		250	
6.3A	140		250	
8A	120		250	
10A	110		250	

PERFORMANCE

CURRENT		2.1 In		2.75 In		4 In		10 In	
		MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
TOTAL OPERATING TIME	1A - 3.15 A	-	30 Mins	200mS	80 S	50mS	5 S	6mS	55mS
	4A - 10A	-	30 Mins	1 S	80 S	150mS	5 S	20mS	100mS

BREAKING CAPACITY
1500 A. 250V. P.f. 0.7-0.8

ENDURANCE
1h @ 1.05 In FOLLOWED
BY 15 Mins OFF REPEATED
100 TIMES THEN 1h @
1.2 In.



All goods are sold and services and advice rendered in connection therewith subject only to the Company's Standard Conditions of Sale

1	4151	3.4.84
ISS	REVISION	DATE




COOPER (UK) LIMITED Beswick, Frome, Somerset, BA11 1PP, England

HIGH BREAKING CAPACITY
CERAMIC CARTRIDGE SILVERED CAPS

TIME - LAG

Beswick Type Ref
TDC 459

SPECIFICATION



MARKING
BARREL PRINT.
ALERT.
T RATED CURRENT.
RATED VOLTAGE


RATED CURRENT	MAX mV DROP @ In	RATED VOLTAGE	
		AC	
1A	350	250	
1.25A	300	250	
1.6A	250	250	
2A	250	250	
2.5A	200	250	
3.15A	180	250	
4A	160	250	
5A	150	250	
6.3A	140	250	
8A	120	250	
10A	110	250	

PERFORMANCE

CURRENT		2.1In		2.75 In		4 In		10 In	
		MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
TOTAL	1A - 3.15 A	-	30Mins	200mS	80 S	50mS	5S	6mS	55mS
OPERATING TIME	4A - 10A	-	30Mins	1S	80 S	150mS	5 S	20mS	100mS

BREAKING CAPACITY
1500 A. 250V. P.f. 0.7-0.8

ENDURANCE
1h @ 1.05 In FOLLOWED
BY 15Mins OFF REPEATED
100 TIMES THEN 1h @
1.2 In.



All goods are sold and services and advice rendered in connection therewith subject only to the Company's Standard Conditions of Sale


1	4151	3.4.84
ISS	REVISION	DATE



BUSSMANN

COOPER (UK) LIMITED Beswick, Frome, Somerset, BA11 1PP, England

TIME - SECONDS



TIMES RATED CURRENT

TIME CURRENT CHARACTERISTIC

DRG No

TDC 459

RATINGS

10 A


ISS	1	REVISION	4161	DATE	19.7.84.
DRN	Q.H.	APPD			

Beswick a division of Dubilier plc
 Alert Works, Frome, Somerset BA11 1PP, England
 Telephone Frome (0373) 64311

DISTRIBUTION V



TIME - SECONDS



TIME CURRENT CHARACTERISTIC

DRG No

TDC 459

RATINGS

10 A

ISS	1	REVISION	4161	DATE	19.4.84
DRN	24	APPD			

Beswick a division of Dублин plc
 Alert Works, Frome, Somerset BA11 1PP, England.
 Telephone: Frome (0373) 64311

DISTRIBUTION V

TIMES RATED CURRENT

29