

## Maschinengewindebohrer-Sätze HSS, HSS Co 5, HSS Co 5-VAP für VA Stähle und HSS-TiN in Industriekassette



Nr. 245 061



Nr. 245 062



Nr. 245 063



Nr. 245 064



Nr. 245 065



Nr. 245 066



Nr. 245 051



Nr. 245 052

Benennung	Artikel-Nr. HSS	Artikel-Nr. HSS Co 5	Artikel-Nr. HSS Co 5-VAP	Artikel-Nr. HSS-TiN
7-teiliger Maschinengewindebohrer-Satz M DIN 371 / 376 Form B mit Schälanschnitt M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12	245 057	245 061	245 063	245 065
7-teiliger Maschinengewindebohrer-Satz M DIN 371 / 376 Form C / 35° RSP M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12	245 058	245 062	245 064	245 066
14-teiliger Maschinengewindebohrer-Satz 7 Maschinengewindebohrer M DIN 371 / 376 Form B mit Schälanschnitt M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 Spiralbohrer DIN 338 Typ N Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm	—	245 051	—	—
14-teiliger Maschinengewindebohrer-Satz 7 Maschinengewindebohrer M DIN 371 / 376 Form C / 35° RSP M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 Spiralbohrer DIN 338 Typ N Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm	—	245 052	—	—
21-teiliger Maschinengewindebohrer-Satz 7 Maschinengewindebohrer M DIN 371 / 376 Form B mit Schälanschnitt M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 Maschinengewindebohrer M DIN 371 / 376 Form C / 35° RSP M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 Spiralbohrer DIN 338 Typ N Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm	—	245 054	—	—