




Item	Date	Remark
X1	20070822	Refer to OS128064PK27MY0B00 Code H5550



Pin	Symbol
1	N.C. (GND)
2	VCC
3	VCOMH
4	IREF
5	D7
6	D6
7	D5
8	D4
9	D3
10	D2
11	D1
12	D0
13	ERD#
14	R/W#
15	D/C#
16	RES#
17	CS#
18	N.C.
19	BS2
20	BS1
21	VDD
22	N.C.
23	N.C.
24	N.C.
25	N.C.
26	N.C.
27	N.C.
28	N.C.
29	VSS
30	VSL

- Notes:
- Color: Yellow
 - Driver IC: SSD1325
 - TCP Number: SSD1325T6
FPC Number: TBD
 - Interface:
8-bit 68XX/80XX Parallel, 4-wire SPI
 - General Tolerance: ±0.30

Customer Approval Signature	DD12864-YO-1A						Drawing Number	Rev.		
							I070805	X1		
	Unless Otherwise Specified		Title	I070805 Folding Type OEL Display Module Pixel Number: 128 x 64, Monochrome, TCP+FPC Package				Material		
	Unit	mm						Soda Lime / Polyimide		
	General Roughness		Tolerance	Drawn	E.E.	Panel / E.	P.M.	Scale	Sheet	Size
	Dimension	±0.3		By	Humphrey Lin			1:1	1 of 1	A3
	Angle	±1	Date	20070822						