

HL 1610 S

1600 W
300/500 °C
240/450 l/min.



Attractively priced entry-level model with two heating and airflow stages for all standard hot air applications.

With this entry-level model, the brand leader offers a tried and tested, robust tool for all applications up to 500°C that don't require the use of reduction nozzles. A resettable thermostat additionally provides effective overheating protection determined by legal legislation.

Settings

- Temperature and airflow can be adjusted in 2 stages at the operating switch: 240 l/min., 300°C; 450 l/min., 450 °C.

Features

- Double overheating protection: thermostat and thermal fuse.
- Industrial grade rubber power cord.
- Hand-held and self-resting.

Example applications for heat gun HL 1610 E

Lighting barbecues



Thawing water pipes



Paint stripping



Drying paint



Waxing snowboards



Shrinking cable sleeves

HL 1610 S

Item No.	348014	
Dimensions (lxwxh)	240 x 89 x 200 mm	
Output	1600 W	
Voltage	230 – 240 V, 50 Hz	
Stage	1	2
Airflow rate	240 l/min.	450 l/min.
Temperature	300°C	500°C
Temperature setting	2-stage	

Temperature display
Weight

–
700 g
Subject to technical modifications