

# Product Data Sheet

## STRONGOPLUS

### ANTI-STATIC 834

artnr. N2834x060



PVC GLOVES



**Description:** Black PVC supported Chemical Resistant Gloves. Lightweight design for delicate jobs, where flexibility and dexterity are important. Ideal for use with certain light oils and chemicals. The PVC has been designed to have Anti-Static properties making the gloves ideal for use in potentially explosive atmospheres.

**Dimensions:** Length: 834 = 40cm  
Sizes Available: 9 / 9.5 / 10.5 (EN420)

**Materials:** 100% cotton interlock lining coated with lightweight black PVC, with a gimped cuff.

**Standards:** 0086 CE. EN420, EN388, EN374.

<b>*Mechanical Performance to EN388:</b>	Abrasion	Level 4	<b>*All testing performed by:</b> SGS, YARSLEY I.C.S., Camberley, Surrey GU15 3EY Notified Body No: 0120
	Blade Cut	Level 1	
	Tear	Level 2	
	Puncture	Level 1	
	Anti-Static	Pass	

**\*Penetration to EN374:** Level 1

<b>*Chemical Performance to EN374:</b>	<u>Reagent</u>	<u>Level</u>	<u>Time</u>
	37% Hydrochloric Acid	6	> 8 hrs
	40% Sodium Hydroxide	6	> 8 hrs
	65% Nitric Acid	3	1 hr 13min
	98% Sulphuric Acid	2	57 min

**Packaging:** 50 pairs per carton, bundled in 5 pairs

PDS 24-11-2000

North Safety Products Europe by postbus 5016, 4330KA, Middelburg - Holland