



Cirrus 80			
Nominal Power Output at 10°C	300/600W	450/800W	
Typical max inrush current	at 230 AC, amps at 115 AC, amps	10 15	11 14
Fan volumetric flow, approximate, m3/hr	35	35	
Fan lifetime at 40°C L10, hours	52,500	52,500	
Normal input voltage	115V or 230VAC	115V or 230VAC	
Dimensions	- cross section mm - length mm	82 x 110 150	82 x 110 150
Weight (g)	785	785	
Finger guards inlet and outlet	Y	Y	

### Options

- Filter Assembly\*
- Fixing - 35mm DIN clip

\* Typical power reduction of 10% when 30PPI filter fitted

Data is given for illustration purposes only and does not release the customer from independent application tests. This information is subject to change without notice.