


5

4

3





2

1



vorverrastet
pre assembled
preassemble

verrastet
fitted
assemble



1) Markierung erster Kontakt, Ader 2 des Flachkabels
 1) Contact no.1, 1st wire of flat cable
 1) Contact no.1, repère 1 du câble

D
C
B
A



All Dimensions in mm
Original Size DIN A 4

Techn. Character.

Nicht tolerierte Masse/ Free size tolerances

09185105803
09185106803
09185107803

0,76 $\mu\text{m Au}$
2
3

	Dat.	Name
Detail.	01-FEB-00	Th
Insp.	01-FEB-00	JMV
Stand.		

Massstab/Scale
2:1

SEK 18 Female connector
10 poles
with central polarisation
cover without cable stop

Bestell-Nr.
Part-No.
Reference

Anforderungsstufe
performance level
Niveau de qualite

27570	01-FEB-00	JB
Mod.	Dat.	Name

HARTING EURL
F-95972 Paris



TB 0918510X803
Sub.

Blatt/ page
1/1