



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


#### REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1906	A	RELEASED	EO	04/17/06	TL	5/25/06	HO	5/25/06



RoHS  
Compliant



#### Specifications:

- Molded connector end requirements:
  - Inner mold using PE
  - Aluminum foil wrap to connector
  - PVC - 45P, Platinum gray
- Cable:

[28AWG (7/0.12)\*9C+AL/MY+DW(7/0.16)]TIN

Wire: OD=0.78±0.03mm


Color: COLOR CODE

Jacket: PVC, OD = Ø5.0±0.15mm

Color: Platinum gray
- Thumbscrew: Male 4X47mm, Nickel plating
- Connector: DB9P Male, Nickel plating, Insulator Color: Blue
- Connector: DB9P Female, Nickel plating, Insulator Color: Blue
- (Screw)Nut: 4.75\*6mm Nickel plating

#### PIN OUTS

DB9P MALE	WIRE COLOR	DB9P FEMALE
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	WHITE	9
SHELL		SHELL



SECTION A-A

SPC TYPE No.	LENGTH
SPC19944	72±1 [1829±25.4]
SPC19943	120±2 [3048±50.8]
SPC20036	300±3 [7625±76.2]

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

#### TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
EKLAS ODISH	04/17/06
CHECKED BY:	DATE:
THOMAS LEE	5/25/06
APPROVED BY:	DATE:
HISHAM ODISH	5/25/06

#### DRAWING TITLE:

Serial Mouse Data Cable, DB9P Male/Female

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-720	TA-720.DWG	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	