

Retractors

RB Retractors

0.5 - 1.8 kg 1.0 - 4.0 lb



RF Retractors

1.8 - 3.6 kg 4.0 - 8.0 lb



F Retractors

0.4 - 10.0 kg 1.0 - 22.0 lb



RB and RF Retractors

- Heavy-duty, long-life spring for lasting performance
- Easy tension adjustment - no tools required
- RB retractor has a 360° swivel hanger for a full range of motion
- RF retractor features a 360° forged steel swivel hanger
- Quick installation
- Durable nylon cord for long life and reduced maintenance (RB)
- Convenient snap-type tool clip for easy tool handling
- RF comes with nylon coated stranded steel cable
- Alignment of hanger and tool hook for smooth, efficient use

part no.	weight range (kg)	travel (m)	weight range (lb)	travel (ft.)
RB2	0.5 - 0.9	1.6	1.0 - 2.0	5.2
RB4	0.9 - 1.8	1.6	2.0 - 4.0	5.2
RB210	0.5 - 0.9	3.04	1.0 - 2.0	10

part no.	weight range (kg)	travel (m)	weight range (lb)	travel (ft.)
RF6	1.8 - 2.7	2.0	4.0 - 6.0	6.6
RF8	2.7 - 3.6	2.0	6.0 - 8.0	6.6

F Retractors

- Easy tension adjustment with no special tools required
- Heavy-duty steel construction for long life
- Long-lasting main spring designed to minimize spring flexing and fatigue
- Tool can be set at desired position with adjustable cable stop
- Durable 2.5 mm diameter stranded steel aircraft cable

part no.	weight range (kg)	travel (m)	weight range (lb)	travel (ft.)
5F	0.4 - 2.3	2.4	1.0 - 5.0	8
10F	1.8 - 4.5	2.4	4.0 - 10.0	8
15F	3.6 - 6.8	2.4	8.0 - 15.0	8
22F	7.3 - 10.0	2.4	16.0 - 22.0	8