

Fan Kits



Filter Fan Grills

- Mounts easily with 4 screws using the template provided.
- All mounting hardware included.
- Standard 80mm/3.15" and 120mm/4.00" fans can be attached with hardware provided to make a filter fan.
- Can be used alone as an enclosure exhaust.
- Moulded in flame retardant ABS.
- Flame retardant synthetic filter supplied.
- Integral gasket on reverse of grill seals against enclosure surface.
- Available in black, RAL7032 beige and ASA61/RAL7011 gray to match enclosures.

Accessories

- Spare hardware kit, Part No. **1421F4**

Black Part No.	Beige Part No.	Gray Part No.	H	W	Optional Compatible Fan Part No.	Size	CFM	Repl. Filter (pkg, 5)
XPFA80BK	XPFA80CG	XPFA80GY	4.13	4.13	FAN80AC115	80mm/3.15"	32	PFF1000
XPFA120BK	XPFA120CG	XPFA120GY	5.91	5.91	DNMF100AC115	120mm/4.70"	102	PFF2000

Climate Control

AC Fans and Guards



Fan Cords and Daisy Chains (10 amp, 115V)

Part No.	Description	Lead Length (In)	Connector	Fan End Termination
DNMFC	Fan Cord	24"	Straight	none
DNFC48P	Fan Cord	48"	45°	2 pin 115V plug
DNFC72P	Fan Cord	72"	45°	2 pin 115V plug
DNFDC2P	Daisy Chain	24"	2x45°, 24" apart	2 pin 115V plug
DNFDC3P	Daisy Chain	24"	3x45°, 24" apart	2 pin 115V plug

Part No.	Size (mm)	Size (In.)	CFM	AC Voltage	Use Fan Guard	Use Filter Fan Grill
FAN80AC115	80	3.15	32	115	FAN80FG	XPFA80... ¹
FAN80AC230	80	3.15	32	230	FAN80FG	XPFA80... ¹
DNMF100AC115	120	4.70	100	115	DNFG	XPFA120... ¹
DNMF100AC230	120	4.70	100	230	DNFG	XPFA120... ¹
FAN150AC115	150	6.00	210	115	FAN150FG	n/a
FAN150AC230	150	6.00	210	230	FAN150FG	n/a
FAN10A115	255	10.00	550	115	FAN10FG	n/a
FAN10A220	255	10.00	550	230	FAN10FG	n/a

¹"..." specify color - BK (black), CG (RAL 7032) or GY (ASA61 gray)

UL recognized, CSA listed, CE certified