

Sensor, Thermocouple, Type K, Mineral Insulated, Miniature Plug

1.5mm & 3.0mm Diameter



- Type K mineral insulated thermocouples
- Particularly suitable for high pressure, vacuum or vibration applications
- Quick, simple connection for easy installation
- 220°C Miniature plug termination
- 310 Stainless steel sheath with welded tip
- Sensor temperature range from -100°C to 1100°C

Probe Dia. (mm)	Probe Length (mm)	Farnell Code	Lab Data Reference	Lab Stock Code
0.5	150	4248296	XF-339-FAR	MB-ISK-S05-150MP
0.5	250	4248302	XF-340-FAR	MB-ISK-S05-250MP
0.5	500	1289600		MB-ISK-S05-500MP
0.5	1000	1289601		MB-ISK-S05-1000MP
1.5	150	4248314	XF-341-FAR	MB-ISK-S15-150MP
1.5	250	4248326	XF-342-FAR	MB-ISK-S15-250MP
1.5	500	1289602		MB-ISK-S15-500MP
1.5	1000	1289604		MB-ISK-S15-1000MP
3.0	150	4248338	XF-343-FAR	MB-ISK-S30-150MP
3.0	250	4248340	XF-344-FAR	MB-ISK-S30-250MP