



Selection and ordering data

Design	Order No.	Price 1 unit	Pack Unit
LOGO! basic devices without display			
6ED1 052-2FB00-0BA4 	LOGO! 12/24RCo Supply voltage DC 12/24 V 8 digital inputs DC 12/24 V, of which 2 can be used as analog (0 to 10 V), 4 relay outputs 10 A Integrated clock Without display and keyboard	6ED1 052-2MD00-0BA4	1
	LOGO! 24RCo Supply voltage AC 24 V 8 digital inputs AC 24 V 4 relay outputs 10 A Integrated clock Without display and keyboard	6ED1 052-2HB00-0BA4	1
	LOGO! 230RCo Supply voltage AC/DC 115, 230 V 8 digital inputs AC/DC 115, 230 V 4 relay outputs 10 A Integrated clock Without display and keyboard	6ED1 052-2FB00-0BA4	1
LOGO! basic devices with display			
6ED1 052-1HB00-0BA4 	LOGO! 24 Supply voltage DC 24 V 8 digital inputs DC 24 V, of which 2 can be used as analog (0 to 10 V), 4 digital outputs DC 24 V, 0.3 A	6ED1 052-1CC00-0BA4	1
	LOGO! 24o Supply voltage DC 24 V 8 digital inputs, 4 digital outputs, transistor output, no clock 2 analog ins, no display	6ED1 052-2CC00-0BA4	1
	LOGO! 12/24RC Supply voltage DC 12/24 V 8 digital inputs DC 12/24 V, of which 2 can be used as analog (0 to 10 V), 4 relay outputs 10 A Integrated clock	6ED1 052-1MD00-0BA4	1
	LOGO! 24RC Supply voltage AC 24 V 8 digital inputs AC 24 V 4 relay outputs 10 A Integrated clock	6ED1 052-1HB00-0BA4	1
	LOGO! 230RC Supply voltage AC/DC 115, 230 V 8 digital inputs AC/DC 115, 230 V 4 relay outputs 10 A Integrated clock	6ED1 052-1FB00-0BA4	1

6ED1

Selection and ordering data

Design	Order No.	Price 1 unit	Pack Unit
Expansion modules			
6ED1 055-1CB00-0BA0 	LOGO! DM8 24 Supply voltage DC 24 V 4 digital inputs DC 24 V, 4 digital outputs DC 24 V, 0.3 A	6ED1 055-1CB00-0BA0	1
	LOGO! DM8 12/24R Supply voltage DC 12/24 V 4 digital inputs DC 12/24 V, 4 relay outputs 10 A	6ED1 055-1MB00-0BA1	1
	LOGO! DM8 230R Supply voltage 115, AC 230 V 4 digital inputs 115, AC 230 V 4 relay outputs 10 A	6ED1 055-1FB00-0BA1	1
	LOGO! DM8 24R Supply voltage 24 V AC 4 inputs, 4 outputs relay output	6ED1 055-1HB00-0BA0	1
6ED1 055-1MB00-0BA0 	LOGO! AM2 Supply voltage DC 12/24 V 2 AI alternatively 0 to 10 V or 0 to 20 mA Resolution 10 bit Sensor supply: not available	6ED1 055-1MA00-0BA0	1
	LOGO! AM2 PT 100 Temperature module Supply voltage 24 V DC 2 analog inputs with PT 100 direct connect for temperature control	6ED1 055-1MD00-0BA0	
Communication modules			
	LOGO! AS-Interface AS-Interface slave; supply voltage DC 24 V 4 digital inputs, 4 digital outputs	3RK1 400-0CE10-0AA2	1
Optional accessories			
6ED1 057-4CA00-0AA0 	LOGO! Manual <ul style="list-style-type: none">• German• English• French• Italian• Spanish• Portuguese	6ED1 050-1AA00-0AE4	1
		6ED1 050-1AA00-0BE4	1
		6ED1 050-1AA00-0CE4	1
		6ED1 050-1AA00-0EE4	1
		6ED1 050-1AA00-0DE4	1
		6ED1 050-1AA00-0GE4	1
	LOGO! Memory card allows copying and saving the program utilizing password protection	6ED1 056-4BA00-0AA0	1
6EP1 331-1SH01 	LOGO!Soft Comfort V4.0 User-friendly programming software programme generation using Drag&Drop Simulation Detailed programme documentation Windows 95 and higher, Linux Detailed online help in German / English / French / Italian / Spanish / Portuguese	6ED1 058-0BA00-0YA0	1
	LOGO!Soft Comfort Upgrade Upgrade from V1.0, V2.0, V3.0 to 4.0	6ED1 058-0CA00-0YE0	1
	LOGO! PC cable for transferring control programmes from a PC to LOGO! and vice versa	6ED1 057-1AA00-0BA0	1
	LOGO!Contact Switching module for direct switching of resistive loads up to 20 A and motors up to 4 kW <ul style="list-style-type: none">• 24 V• 230 V	6ED1 057-4CA00-0AA0	1
		6ED1 057-4EA00-0AA0	1
	LOGO!Power Power supply to convert the line voltage AC 120/230 V to the operating voltage DC 24 V or DC 12 V <ul style="list-style-type: none">• LOGO! Power 24 V/1.3 A• LOGO! Power 24 V/2.5 A• LOGO! Power 12 V/1.9 A• LOGO! Power 12 V/4.5 A	6EP1 331-1SH01	1
		6EP1 332-1SH41	1
		6EP1 321-1SH01	1
		6EP1 322-1SH01	1

Selection and ordering data

Design	Order No.	Price	Pack
		1 unit	Unit
Optional accessories			
LOGO! News Box, 12/24 V Contents: LOGO! 12/24RC, LOGO! PC cable, LOGO!Soft Comfort V3.0, LOGO! Starter kit			
• German	6ED1 057-3BA00-0AA3		1
• English	6ED1 057-3BA00-0BA3		1
LOGO! News Box, 230V Contents: LOGO! 230RC, LOGO! PC cable, LOGO!Soft Comfort V3.0, LOGO! Starter kit			
• German	6ED1 057-3AA00-0AA8		1
• English	6ED1 057-3AA00-0BA8		1
LOGO! Prom for writing and copying LOGO! memory submodules	6AG1 057-1AA01-0AA0		1
LOGO! mounting kit 4TE for front panel installation, mounting dimensions (WxHxD) 79x95x57 mm, IP30 without plexi washer, IP65 with plexi washer	6AG1 057-1AA00-0AA0		1
LOGO! mounting kit 8TE for use with LOGO! basic plus 2 expansion modules, IP65 rated	6AG1 057-1AA00-0AA1		1
LOGO! mounting kit 8TE for use with LOGO! basic plus 2 expansion modules with function keys and membrane style function keys to operate cursor keys on the face of the unit	6AG1 057-1AA00-0AA2		1

