


DURACELL® Rechargeable



Rechargeable Supreme AA



BENEFITS

- Recharge 100s of Times to Capture 1000s of Pictures
- Ideal for Digital and High Drain Devices

TECHNICAL

Type:	NiMH AA 2450 mAh
Nominal Voltage	1.2V
Nominal Internal Impedance:	25 m-ohm @ 1kHz
Average Weight:	30.2 grams (1.07 ounces)
Volume:	8.3 cm ³ (0.50 in ³)
Operating Temperature Range:	-20° C to 50° C (-4° F to 122° F)
ANSI:	1.2H1
IEC:	HR6
Product Codes:	Blister x2 – EU/UK SAP Code: 75070715 EU/UK EAN Code: 5000394203679 Blister x4 – EU/UK SAP Code : 75070716 EU/UK EAN Code : 5000394203686

Dimensions shown are IEC standards

Product can be charged on most NiMH or NiCd chargers utilizing standard dV, dV/dt, time and temperature dynamic charge termination methods. Duracell brand NiMH chargers are recommended for best results.

Delivered capacity is dependent on the applied load, operating temperature, and cut-off voltage. Please refer to the charts and discharge data shown for example of the energy/service life that the battery will provide for various local conditions.

This data is subject to change. Performance information is typical. Contact Duracell for latest information.

