



72-8700 PRODUCT SPECIFICATIONS

Feature		
Output Voltage	Ch1, Ch2	0~32V
	Ch3	
Output Current	Ch1, Ch2	0~5A
	Ch3	
Overload Effect	CV $\leq 1 \times 10^{-4} + 2mV$, CC $\leq 2mA$	
Ripple & Noise	CV $\leq 1mV_{rms}$, CC $\leq 1mA_{rms}$	
Regulation	CV - 20mV (Typical Value), CC - 50mV (Typical Value)	
Tracking Error	$5 \times 10^{-3} + 2mV$	
Reliability	MTBF (e): ≥ 2000 hours	
Other Features	Triple Output, Series or Parallel Operation, Current Limitation Auto Switching Between Voltage and Current Operation	

GENERAL CHARACTERISTICS

Power	220V $\pm 10\%$, 50Hz $\pm 4\%$
Product Net Weight	Around 4kg
Product Size	210mm x 152mm x 305mm
Standard Accessories	English Manual and Power Cord
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	2pcs
Standard Carton Measurement	600 x 380 x 245mm (0.056 CBM Per Export Carton)
Standard Carton Gross Weight	9.5kg

Specifications and other information are subject to change without further notice.