




97 52 63 Four-Mandrel Crimping Pliers for turned contacts



PATENTED  

Technical details

No.	97 52 63	
EAN	4003773050148	
Pliers	nickel plated	
Handles	with multi-component grips	
Applications	turned contacts	
Capacity	0,08 - 2,5	mm ²
AWG	28 - 13	
Number of crimping positions	1	
	180	mm
	388	g
	388	g

Description

- for crimping turned contacts
- four-mandrel crimping for top-quality crimping connections
- mandrel gauge to check the basic setting
- repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- optimum transmission of force due to lever action for fatigue-reduced operation
- high operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

Model:

- fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- pliers in the plastic case with foam insert and locator for holding the contacts

Special



Turned contacts are used for particularly demanding plug-type connections, e.g. in medical industry and aeronautics. Extremely reliable crimping connections can be achieved only with pliers that work with absolute precision and maintain the required crimping depth in the 1/100 mm range.