Product data sheet Characteristics

13441

Kaedra enclosure - for modular devices - 4 modules - terminal blocks



Main

mann	
Enclosure type	Weatherproof enclosure
Range of product	Kaedra
Device short name	Kaedra for modular devices
Accessories included with enclosure	1 marking kit 2 terminal blocks 4 holes

Complementary

Enclosure mounting	Surface
Type of front cover	Transparent
Number of horizontal rows	1
Number of 18 mm modules per row	4
Total number of 18 mm modules	4
Type of rail	DIN
Number of pre-cutouts PG ISO	3
Number of terminal blocks	2 4
Distribution block outgoers	4 x 10 mm ² 4 x 16 mm ²
Locking options description	Optional keylock
Enclosure material	Plastic
Width	123 mm
Height	200 mm
Depth	112 mm
Colour	Light grey RAL 7035 enclosure Transparent green door

Environment

Standards	EN 50102	
	EN 50262	
	IEC 60439-3	
	IEC 60529	
	IEC 60695-2-1	
	IEC 670	
Fire resistance	650 °C IEC 60695-2-1	
IP degree of protection	IP65 IEC 60529	
IK degree of protection	IK09 EN 50102	
Electrical shock protection class	Class II	
Ambient air temperature for operation	-2560 °C	
RoHS EUR conformity date	0648	
RoHS EUR status	Compliant	