

RCD Socket Outlets/Fused Connection Units

13A DP RCD Sockets

NEW



X585MG

NEW REF:	
X585MG	RCD Protected Socket Passive 10mA
X586MG	RCD Protected Socket Passive 30mA
X587MG	RCD Protected Socket Active 10mA
X588MG	RCD Protected Socket Active 30mA

- Added protection against electrocution
- Active or Passive switching
- 10mA or 30mA protection

PASSIVE - The contacts on the Passive device remain closed when the mains supply is interrupted - this type is suitable for appliances such as fridge freezers etc.

ACTIVE - The contacts on the Active device open when the mains supply is interrupted - this type is suitable of Power tools, lawnmowers, hedge trimmers etc.

Dimensions
2G - 86mm x 146mm

Fixing centres
2G - 120.7mm

Complete with mounting box.

13A DP Fused Connection Units - Switched



X201MG



X201NMG

NEW REF:	OLD REF:
X201MG	(FM3242)
DP with optional c/outlet	
X201NMG	(FM3244)
DP with neon + optional c/outlet	

To BS 1363: Part 4: 1995

Live and neutral up to 3 x 4mm² or 2 x 6mm² conductors. Separate earth terminals are provided for standard and hard wiring connections.

Dimensions:
1G - 86mm x 86mm

Fixing centres:
1G - 60.3mm

Complete with mounting box.

13A Connection Units - Unswitched



X200MG



X200NMG

NEW REF:	OLD REF:
X200MG	(FM3246)
Unswitched with optional c/outlet	
X200NMG	(FM3248)
Unswitched with neon + optional c/outlet	

To BS 1363: Part 4: 1995

Live and neutral up to 3 x 4mm² or 2 x 6mm² conductors. Separate earth terminals are provided for standard and hard wiring connections.

Dimensions:
1G - 86mm x 86mm

Fixing centres:
1G - 60.3mm

Complete with mounting box.