

8522 Hook-up/Lead - (Type MW) MIL-W-76C-PVC

 For more Information
 please call

1-800-Belden1

**Description:**

Tinned copper, PVC insulation, medium wall. The extruded PVC insulation is flame and ozone resistant. Inert to most chemicals, oils, and solvents. Covers single cond., PVC insulated hook-up wire for internal wiring of electrical and electronic equipment.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
1	18	16x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.4318

Overall Insulation**Overall Cabling**

Overall Nominal Diameter: 2.032 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	MIL-W-76C
MIL Spec Rating:	1000 V, 80°C

Plenum/Non-Plenum

Plenum (Y/N): No

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8522 001100	30 MT	0.363 KG	BROWN		18 STR PVC BRN
8522 0011000	305 MT	3.629 KG	BROWN	P	18 STR PVC BRN
8522 002100	30 MT	0.363 KG	RED		18 STR PVC RED
8522 0021000	305 MT	3.629 KG	RED	P	18 STR PVC RED

METRIC MEASUREMENT VERSION

8522 Hook-up/Lead - (Type MW) MIL-W-76C-PVC

8522 003100	30 MT	0.363 KG	ORANGE		18 STR PVC ORG
8522 0031000	305 MT	3.629 KG	ORANGE	P	18 STR PVC ORG
8522 004100	30 MT	0.363 KG	YELLOW		18 STR PVC YEL
8522 0041000	305 MT	3.629 KG	YELLOW	P	18 STR PVC YEL
8522 005100	30 MT	0.363 KG	GREEN, DARK		18 STR PVC GRN
8522 0051000	305 MT	3.629 KG	GREEN, DARK	P	18 STR PVC GRN
8522 006100	30 MT	0.363 KG	BLUE, LIGHT		18 STR PVC LBLU
8522 0061000	305 MT	3.629 KG	BLUE, LIGHT	P	18 STR PVC LBLU
8522 007100	30 MT	0.363 KG	VIOLET		18 STR PVC VIO
8522 0071000	305 MT	3.629 KG	VIOLET	P	18 STR PVC VIO
8522 008100	30 MT	0.363 KG	GRAY		18 STR PVC GRY
8522 0081000	305 MT	3.629 KG	GRAY	P	18 STR PVC GRY
8522 009100	30 MT	0.363 KG	WHITE		18 STR PVC WHT
8522 0091000	305 MT	3.629 KG	WHITE	P	18 STR PVC WHT
8522 010100	30 MT	0.363 KG	BLACK		18 STR PVC BLK
8522 0101000	305 MT	3.629 KG	BLACK	P	18 STR PVC BLK
8522 0111000	305 MT	3.629 KG	TAN	P	18 STR PVC TAN
8522 0121000	305 MT	3.629 KG	PINK	P	18 STR PVC PNK
8522 013100	30 MT	0.363 KG	BLUE, DARK		18 STR PVC DBLU
8522 0131000	305 MT	3.629 KG	BLUE, DARK	P	18 STR PVC DBLU
8522 014100	30 MT	0.363 KG	WHITE/BLACK	A	18 STR PVC WHT/BLK
8522 0141000	305 MT	3.629 KG	WHITE/BLACK	A	18 STR PVC WHT/BLK
8522 0151000	305 MT	3.629 KG	WHITE/RED	A	18 STR PVC WHT/RED
8522 0161000	305 MT	3.629 KG	WHITE/GREEN	A	18 STR PVC WHT/GRN
8522 018100	30 MT	0.363 KG	WHITE/BLUE	A	18 STR PVC WHT/BLU
8522 0181000	305 MT	3.629 KG	WHITE/BLUE	A	18 STR PVC WHT/BLU
8522 020100	30 MT	0.363 KG	WHITE/ORANGE	A	18 STR PVC WHT/ORG
8522 0201000	305 MT	3.629 KG	WHITE/ORANGE	A	18 STR PVC WHT/ORG
8522 0241000	305 MT	3.629 KG	WHITE/BLACK/GREEN	A	18 STR PVC WHT/BLK/GRN
8522 0261000	305 MT	3.629 KG	WHITE/BLACK/BLUE	A	18 STR PVC WHT/BLK/BLU
8522 029100	30 MT	0.363 KG	YELLOW/BLACK	A	18 STR PVC WHT/BLK/GRY
8522 0301000	305 MT	3.629 KG	WHITE/BLACK/VIOLET	A	18 STR PVC WHT/BLK/VIO

Notes:

A = STOCKED STRIPE COLORS.

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL

Revision Number: 1 Revision Date: 05-14-2007

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.