



408



| Torx |     |     |    |     |    |  |  |  |  |  | Item No           |     | EAN-Code         |
|------|-----|-----|----|-----|----|--|--|--|--|--|-------------------|-----|------------------|
| 7    | 60  | 86  | 25 | 3,0 | 12 |  |  |  |  |  | <b>408 071 40</b> | 28  | 40 07157 52807 0 |
| 8    | 60  | 86  | 25 | 3,0 | 12 |  |  |  |  |  | <b>408 083 40</b> | 28  | 40 07157 52809 4 |
| 9    | 60  | 86  | 25 | 3,5 | 12 |  |  |  |  |  | <b>408 093 40</b> | 28  | 40 07157 52811 7 |
| 10   | 100 | 86  | 25 | 3,5 | 12 |  |  |  |  |  | <b>408 103 40</b> | 33  | 40 07157 52813 1 |
| 15   | 100 | 94  | 30 | 4,0 | 12 |  |  |  |  |  | <b>408 153 40</b> | 50  | 40 07157 52815 5 |
| 20   | 100 | 101 | 33 | 5,0 | 12 |  |  |  |  |  | <b>408 203 40</b> | 68  | 40 07157 52817 9 |
| 25   | 100 | 106 | 36 | 5,0 | 12 |  |  |  |  |  | <b>408 253 40</b> | 82  | 40 07157 52819 3 |
| 27   | 100 | 106 | 36 | 5,0 | 12 |  |  |  |  |  | <b>408 273 40</b> | 82  | 40 07157 52821 6 |
| 30   | 115 | 112 | 39 | 6,0 | 6  |  |  |  |  |  | <b>408 303 40</b> | 103 | 40 07157 52823 0 |
| 40   | 125 | 112 | 39 | 8,0 | 6  |  |  |  |  |  | <b>408 404 40</b> | 136 | 40 07157 52825 4 |

M-TEC

428



| mm  |     |     |    |  |  |    | Item No           |     | EAN-Code         |
|-----|-----|-----|----|--|--|----|-------------------|-----|------------------|
| 5,5 | 110 | 94  | 30 |  |  | 12 | <b>428 055 30</b> | 84  | 40 07157 60285 5 |
| 6   | 110 | 94  | 30 |  |  | 12 | <b>428 060 30</b> | 87  | 40 07157 60349 4 |
| 7   | 110 | 94  | 30 |  |  | 12 | <b>428 070 30</b> | 97  | 40 07157 60287 9 |
| 8   | 110 | 101 | 33 |  |  | 12 | <b>428 080 30</b> | 110 | 40 07157 60289 3 |
| 10  | 125 | 101 | 33 |  |  | 12 | <b>428 100 30</b> | 126 | 40 07157 60291 6 |
| 13  | 125 | 106 | 36 |  |  | 12 | <b>428 130 30</b> | 187 | 40 07157 60293 0 |

