
## Product data sheet Characteristics

## XZCP1865L5

female, 1/2' 20UNF, 3-pin, straight prewired connector - cable 5 m



Main	
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Pre-wired connectors
Series name	General purpose
Electrical connection	Straight female connector 1/2"20 UNF, 3 pins
Collar material	Metal
Status LED	Without
Cable length	5 m

## Complementary

Cable connector fixing	Screw-on	
Cable outer diameter	5.2 mm	
Cable composition	3 x 0.34 mm²	
Wire insulation material	PUR	
[Ue] rated operational voltage	250 V AC 300 V DC	
[In] rated current	4 A	
Contact resistance	<= 5000 μOhm	
Insulating resistance	>= 1 GΩ	
Product weight	0.18 kg	

## Environment

IP degree of protection	IP67	
Ambient air temperature for storage	-35100 °C	
RoHS EUR status	Compliant	
RoHS EUR conformity date	0649	