

# SONY

**CFD-S05**

Easy to use portable CD Radio Cassette player for music in any format

**Features**

## Specifications

### Tuner

Digital synthesiser tuner	YES
Analogue tuner	NO
Presets	30 (20 FM, 10 AM)
FM (MHz)	87.5 - 108
MW (kHz)	531 - 1,602
External antenna input	NO

### CD

MP3	NO
ID3-tag (CD text)	YES
CD-R	YES
CD-RW	YES
Loop function	NO
Program	YES
Repeat	YES
Shuffle	YES
AMS	NO
CD-Tray	YES
Vertical loading mechanism	NO

### Cassette

Autoreverse	NO
Auto shut off	YES
CD synchronized start	YES
High speed dubbing	NO

### General Data

Mega Bass	YES
Mega Xpand	NO
Bass Reflex Speaker System	YES
MD Link	NO
Electronic sound modes	NO
LCD with backlight	YES
Clock	NO
Timer	NO
Sleep timer	NO
Jog dial	NO
Loudspeaker diameter	2 x 80mm
Power Output: RMS	2 x 1.7 W
Line in	YES
Microphone in	NO
Headphone out	YES
Remote control	NO
Type of battery	C
Number of batteries	6.0
External DC IN	9V

Built in AC adaptor (V)	230
Weight with batteries (kg)	2.7

<b>Dimensions</b>	
Width (mm)	365.0
Height (mm)	134.0
Depth (mm)	230.0

<b>Guarantee</b>	
Guarantee in Months	-