

Technical Information

ICON/HERITAGE/SPT/GRIP-TRAX®

- All styles meet EN345 standards
 - 200 Joule toe cap
 - Incorporates new Grip-Trax® and SPT soles on new models
 - Goodyear welted heat sealed anti-slip air cushioned sole on existing styles; not suitable for heavy engineering work
 - Resistant to acid, oils, solvents and heat up to 80°C
 - Collar ankle and tongue padding. Leather heellock
- ### GRIP-TRAX® EXTRA FEATURES
- Grip-Trax® anti-slip dual material sole heat resistant to 300°C
 - Dri-Lex Workhorse lining with moisture absorbing qualities
 - Ortholite footbed, giving excellent support for daylong comfort
 - KEVLAR reinforced, strong and durable rubber toeguard
 - Flexible TPU moulded side foot stability control system for maximum support



Safety

GRIP-TRAX



Safety



Safety

SHEFFIELD II/STOCKTON/TRAINERS

- All styles meet EN345 standards
- 200 Joule toe cap, speed lacing with collar and tongue padding
- Incorporates NEW Techni flex™ sole with full grain leather uppers, together with EVA midsole on Sheffield II styles
- Goodyear welted, except trainers
- Split leather on Stockton styles
- Anti-slip soles
- Cambrelle lined to absorb foot moisture
- All styles resistant to acid, oils, solvents and heat up to 300°C

Briggs

Safety With Style



CE EN345-1 SB E ORO HIRO



6900
GRIP-TRAX®
Black
Sizes 3-13



GRIP-TRAX® PU Rubber
Anti Slip Sole



6901
GRIP-TRAX®
Black
Sizes 3-13

NEW



6902
GRIP-TRAX®
Gaucho
Sizes 3-13

