

LUMBERJACK WOODWORM KILLER

Colour	Product Code	Pack Size	Box Qty
Clear	LJWORM01	1ltr	10
Clear	LJWORM05	5ltr	4

Product Description

LUMBERJACK WOODWORM KILLER is a ready to use treatment for the eradication of all types and life stages of wood boring insects and their larvae, specifically woodworm. It is a low solvent; low odour solution based on Micro-fine active technology with added insecticide to penetrate deep into the wood to actively kill and protect against re-infestation.

LUMBERJACK WOODWORM KILLER is fast drying and non flammable.

Benefits

- Kills all types of wood boring insects
- Penetrates deep into the wood for long lasting protection
- For interior use only
- Overpaintable

Areas for use

LUMBERJACK WOODWORM KILLER can be used on most internal furniture, woodwork and joinery such as doors, window frames, roof timbers, floorboards, joists, rafters, etc. It can be over painted, stained, varnished, or polished when dry if required.

Limitations

- Ready to use - do not dilute.
- Do not use in food preparation areas.
- Do not use externally.
- It is the user's responsibility to determine suitability for use. If in doubt, contact Technical Services Department for advice.

Surface Preparation

Ensure that timber to be treated is clean. Any paint or other surface coatings should be removed prior to application. Remove any badly infected or structurally unsound timber and replace with sound timber prior to application.

Application

Read statutory conditions relating to use prior to application.

Shake well before use. Apply by brush, spray or dipping. Apply a minimum of two coats if brushing or spraying. The second coat should be applied after the first coat has soaked in but before it is dry. Pay particular attention to thoroughly soaking the end grain. Where possible, dip or flood the end grains of the timber for maximum protection.

Coverage Guide

Apply 2 coats at a rate of 1 litre of product per 3 - 4m² of surface.

Dip end grains for a minimum of 3 minutes or flood thoroughly where dipping is not possible.

Drying time is approximately 1 hour depending on temperature.

Health & Safety

See MSDS for full list of hazards.

Storage

Store at moderate temperatures in original containers away from children.

Shelf Life

Use within 2 years of manufacture.

The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.