

NBNC75BHK7

The rearTWIST BNC cable connector offers a true 75 Ω design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cable:
Canare L-3CFB

Crimp size:
Pin: 1.6 mm (square) or 1.75 mm (hex)
Shield: 5.41 mm (hex)

Features & Benefits

- "RearTwist® Principe" locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507).
- Ideal for recessed bulkheads where access to the "head" of the connector might be an issue. These connectors turn from the back and not the front.
- True 75 Ω design meets the stringent HD requirements.
- Snug-fit center pin assembly provides tactile feedback.
- Excellent cable protection and retention.
- Precise machined brass parts for outstanding durability.
- Accessories include color coded boots in 10 standard colors, crimp tool and dies.