



A range of automatic wire strippers to cover cable sizes 0.25mm² to 6.00mm². They all operate using a unique system of self adjusting multiple blades which slice cleanly through the insulation but then form around the conductors to give a clean cut without causing any damage.

There are four patterns available:

Micro Strip (MS1) - Fabricated in glass reinforced polyamide. Stripping capacity 0.25mm² to 1.5mm². Particularly suited for stripping fine wires with soft, delicate insulations. Three interchangeable gripping surfaces are supplied (fine, medium & coarse) to suit all types of wire. A wire cutter is also incorporated in the tool. Replacement jaws Order Code 105-955.

MK1FD - Aluminium bodied to withstand the rough treatment of field use. Capacity 0.25mm² to 2.5mm². Replacement jaw assembly for original MK1F, Order Code 215-302.

MK2FC - "Power Strip" glass re-inforced polyamide body weighing only 150g. Stripping capacity 0.25mm² to 6.0mm² PVC insulated, solid or stranded wires and multi-core. The integral cutter will cut up to 6.0mm² stranded wire and 4.0mm² solid copper. Replacement jaws Order Code 105-957.

222639

Description	Mfrs. List No.	Order Code	Price Each
1.5mm ² Stripper/cutter	MS1	440-802	
Replacement jaws	04301	105-955	
2.5mm ² Stripper	MK1FD	440-814	
6.0mm ² Stripper/cutter	MK2FC	440-826	
Replacement jaws	04601/701	215-302	
Replacement jaws for MK2FM	04801	215-302	