TELECOM / FIBER OPTICS ELECTRICAL / ELECTRONICS

ACS

Armored Cable Slitter

- Professional grade tool ideal for slitting the corrugated copper, steel or aluminum armor layer on Fiber Feeder, Central Tube, Stranded Loose Tube fiber optic cables and other armored cables
- Versatile design allows jacket or shield slitting on non-fiber optic configurations as well
- Tool slits outer polyethylene jacket and armor in one operation
 - Performs longitudinal slitting and circumferential (ringing) for end stripping
 - Blade rotates 90 degrees by activating blade lever, allowing easy mid-span preparation (ringing and slitting)
- Adjustable from 0.315" (8 mm) to 1.125" (28.6 mm) cable O.D.
- Contact Customer Service for smaller diameter cable preparation options
- Adjustable blade depth to 5.5mm maximum to accommodate different cable coverings
- "Roller" style cable follower provides cable stability and allows for easier tool movement along the cable
- Rugged anodized aluminum and steel construction
- Made in the U.S.A.
- U.S. Patent Nos.: 505, 056S
- Replacement blade: CB 251-K (37884)
- Height: 5 in (127 mm)
- Max cutting depth: 5.5 mm
- Weight: 10 oz (284 g)
- Part No.: 37880