# Product data sheet Characteristics

## XVBC07

## Ø 70 mm base unit - black



### Main

Range of product	Harmony XVB Universal
Product or component type	Base unit
Component name	XVBC
Indicator bank base type	Standard
Material	Glass reinforced polyamide base unit

### Complementary

Fixing mode	Direct or tube fixing	
Mounting diameter	70 mm	
Product destination	Banks without flash discharge tube unit	
Cable entry	Bottom or side entry	
Assembly style	Customer assembly, up to 5 units	
Terminals description ISO n°1	(COM-1)PW (COM-2)PW (COM-3)PW (COM-4)PW (COM-5)PW (GND)GROUND	
Product weight	0.16 kg	_

#### Environment


Product certifications	CCC CSA C22-2 No 14 GOST UL 508	
Standards	EN/IEC 60947-5-1	
Protective treatment	TC	
Ambient air temperature for storage	-4070 °C	
NEMA degree of protection	NEMA 4X indoor UL 508	
RoHS EUR status	Compliant	
RoHS EUR conformity date	0808	

## XVBC07

### Indicator Bank with "Flash" Discharge Tube Unit

### **Dimensions**

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order



- Base unit (1)
- (2) (3) Illuminated or audible signalling unit XVBC •••, to be ordered separately
- "Flash" unit XVBC •••, to be ordered separately


Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06

# Product data sheet Mounting and Clearance

# XVBC07

### Base Unit for Indicator Banks

## Panel Cut-out for Direct Fixing



## Product data sheet Connections and Schema

# XVBC07

### Illuminated Beacon

## Wiring Diagram

